

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751057

Luminaire Tested: LD4D60D010-EU4DR5555659027-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751057
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR5555659027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6600.6 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751057

CATALOG NUMBER: LD4D60D010-EU4DR5555659027-4LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P751057

CATALOG NUMBER: LD4D60D010-EU4DR5555659027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106	111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96	106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87	100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80	95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74	91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68	86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64	82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59	78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56	74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52	71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	808704
5°	776576
10°	773651
15°	751435
20°	673766
25°	556836
30°	420616
35°	304980
40°	195175
45°	89141
50°	29151
55°	12572
60°	5419
65°	724
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 89141 cd/sqm



TEST NUMBER: P751057

CATALOG NUMBER: LD4D60D010-EU4DR5555659027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	673.8	10.2
10°-20°	1838.8	27.9
20°-30°	2095.5	31.7
30°-40°	1426.5	21.6
40°-50°	491.6	7.4
50°-60°	67.9	1.0
60°-70°	6.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4608.0	69.8
0°-40°	6034.5	91.4
0°-60°	6594.1	99.9
0°-90°	6600.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6600.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7402	
5°	7080	674
15°	6643	1839
25°	4619	2095
35°	2286	1427
45°	577	492
55°	66	68
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751057

CATALOG NUMBER: LD4D60D010-EU4DR5555659027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	7401.6
2.5°	7231.9
5°	7080.5
7.5°	7006.3
10°	6973.2
12.5°	6863.2
15°	6643.1
17.5°	6293.6
20°	5794.7
22.5°	5218.7
25°	4618.9
27.5°	3994.3
30°	3333.9
32.5°	2774.4
35°	2286.5
37.5°	1822.4
40°	1368.4
42.5°	948.4
45°	576.9
47.5°	310.9
50°	171.5
52.5°	101.8
55°	66.0
57.5°	42.2
60°	24.8
62.5°	11.0
65°	2.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)