

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751290

Luminaire Tested: LD4D60D010-EU4DR7055659027-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR7055659027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6205.5 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751290

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P751290

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	535148
5°	533814
10°	532653
15°	532500
20°	527297
25°	495328
30°	441585
35°	352077
40°	233784
45°	139762
50°	72462
55°	38079
60°	13483
65°	233
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 139762 cd/sqm



TEST NUMBER: P751290

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	462.9	7.5
10°-20°	1327.5	21.4
20°-30°	1872.7	30.2
30°-40°	1616.6	26.1
40°-50°	724.0	11.7
50°-60°	189.5	3.1
60°-70°	12.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3663.0	59.0
0°-40°	5279.6	85.1
0°-60°	6193.1	99.8
0°-90°	6205.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6205.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4898	
5°	4867	463
15°	4708	1327
25°	4109	1873
35°	2640	1617
45°	904	724
55°	200	190
65°	1	12
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751290

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4897.9
2.5°	4892.6
5°	4867.1
7.5°	4845.9
10°	4801.0
12.5°	4760.5
15°	4707.6
17.5°	4646.9
20°	4535.0
22.5°	4350.9
25°	4108.7
27.5°	3827.8
30°	3500.1
32.5°	3099.4
35°	2639.6
37.5°	2132.3
40°	1639.1
42.5°	1245.4
45°	904.5
47.5°	623.6
50°	426.3
52.5°	294.2
55°	199.9
57.5°	120.7
60°	61.7
62.5°	19.4
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)