

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P1327652

Luminaire Tested: LDSQA3D13R20W2N902765DE010 3LSQPHR1MMS_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1327652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LDSQA3D13R20W2N902765DE010 3LSQPHR1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
3LSQPHR1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 858.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.36 / 0.33
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1327652
CATALOG NUMBER: LDSQA3D13R20W2N902765DE010 3LSQPHR1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1327652

CATALOG NUMBER: LDSQA3D13R20W2N902765DE010 3LSQPHR1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	100	100	100	98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	97	98	97	96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	98	96	95	94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	96	95	93	92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	92	95	93	92	91
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	93	91	90	89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	92	90	88	87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	91	88	87	86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	89	87	85	85
10	95	90	87	85	95	90	87	85	89	86	84	88	86	84	88	86	84	88	86	84	83

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1100175	1100175	1100175
5°	950411	959279	962841
10°	572136	577487	606220
15°	197893	193257	208662
20°	51977	48898	49026
25°	11326	13663	15544
30°	4872	4872	5011
35°	2733	2418	2565
40°	1214	1371	1551
45°	365	560	560
50°	214	214	214
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 560 cd/sqm



TEST NUMBER: P1327652

CATALOG NUMBER: LDSQA3D13R20W2N902765DE010 3LSQPHR1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	456.9	53.3
10°-20°	347.9	40.5
20°-30°	43.0	5.0
30°-40°	8.1	0.9
40°-50°	2.0	0.2
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	847.8	98.8
0°-40°	855.9	99.8
0°-60°	858.0	100.0
0°-90°	858.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	858.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	6388	6388	6388	6388	6388	
5°	5498	5494	5549	5545	5569	453
15°	1110	1070	1084	1149	1170	348
25°	60	68	72	75	82	41
35°	13	13	12	12	12	8
45°	2	2	2	2	2	2
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1327652
 CATALOG NUMBER: LDSQA3D13R20W2N902765DE010 3LSQPHR1MMS_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	6388.1	6388.1	6388.1	6388.1	6388.1
1°	6358.3	6350.6	6356.7	6343.7	6370.5
2°	6256.6	6248.9	6248.9	6241.3	6245.1
3°	6067.0	6079.2	6071.6	6055.5	6076.2
4°	5808.6	5822.4	5834.6	5835.4	5838.5
5°	5497.5	5493.7	5548.8	5544.9	5569.4
6°	5142.9	5138.3	5162.0	5201.7	5250.6
7°	4753.0	4697.2	4760.7	4840.9	4906.7
8°	4248.5	4263.0	4306.6	4401.4	4454.1
9°	3820.5	3735.6	3828.1	3941.2	3998.6
10°	3271.6	3202.8	3302.2	3421.4	3466.5
12.5°	2059.3	1999.7	2031.8	2157.1	2177.0
15°	1109.9	1070.2	1083.9	1148.9	1170.3
17.5°	566.4	530.5	522.8	564.1	568.7
20°	283.6	275.2	266.8	270.6	267.5
22.5°	131.5	142.9	141.4	133.8	142.9
25°	59.6	68.0	71.9	74.9	81.8
27.5°	36.7	35.2	40.5	43.6	44.3
30°	24.5	23.7	24.5	25.2	25.2
32.5°	17.6	16.8	16.1	16.1	16.8
35°	13.0	13.0	11.5	12.2	12.2
37.5°	9.2	9.2	8.4	9.2	9.2
40°	5.4	6.1	6.1	6.1	6.9
42.5°	3.1	3.8	3.8	3.8	3.8
45°	1.5	2.3	2.3	2.3	2.3
47.5°	0.8	0.8	0.8	1.5	1.5
50°	0.8	0.8	0.8	0.8	0.8
52.5°	0.8	0.0	0.0	0.0	0.8
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)