

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750754

Luminaire Tested: LD4D60D010-EU4DR3555659030-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3555659030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6034.2 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750754

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P750754

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1814078
5°	1771455
10°	1596550
15°	1239175
20°	702846
25°	273433
30°	102016
35°	55914
40°	36542
45°	22251
50°	14159
55°	10001
60°	7320
65°	3981
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22251 cd/sqm



TEST NUMBER: P750754

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1485.4	24.6
10°-20°	2900.2	48.1
20°-30°	1182.8	19.6
30°-40°	283.1	4.7
40°-50°	118.0	2.0
50°-60°	48.8	0.8
60°-70°	15.3	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5568.5	92.3
0°-40°	5851.6	97.0
0°-60°	6018.4	99.7
0°-90°	6034.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6034.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16603	
5°	16151	###
15°	10955	2900
25°	2268	1183
35°	419	283
45°	144	118
55°	52	49
65°	15	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750754

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	16603.2
2.5°	16503.6
5°	16151.4
7.5°	15448.8
10°	14390.3
12.5°	12899.9
15°	10955.0
17.5°	8576.4
20°	6044.8
22.5°	3854.5
25°	2268.1
27.5°	1282.1
30°	808.6
32.5°	567.7
35°	419.2
37.5°	324.2
40°	256.2
42.5°	197.4
45°	144.0
47.5°	107.7
50°	83.3
52.5°	66.1
55°	52.5
57.5°	42.6
60°	33.5
62.5°	24.4
65°	15.4
67.5°	5.4
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)