

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750769

Luminaire Tested: LD4D60D010-EU4DR3555659035-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3555659035-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5687.4 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750769

CATALOG NUMBER: LD4D60D010-EU4DR3555659035-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P750769

CATALOG NUMBER: LD4D60D010-EU4DR3555659035-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1709789
5°	1669619
10°	1504764
15°	1167936
20°	662441
25°	257724
30°	96149
35°	52700
40°	34445
45°	20968
50°	13343
55°	9429
60°	6905
65°	3749
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20968 cd/sqm



TEST NUMBER: P750769

CATALOG NUMBER: LD4D60D010-EU4DR3555659035-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1400.1	24.6
10°-20°	2733.5	48.1
20°-30°	1114.8	19.6
30°-40°	266.8	4.7
40°-50°	111.2	2.0
50°-60°	46.0	0.8
60°-70°	14.4	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5248.4	92.3
0°-40°	5515.2	97.0
0°-60°	5672.4	99.7
0°-90°	5687.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5687.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15649	
5°	15223	###
15°	10325	2734
25°	2138	1115
35°	395	267
45°	136	111
55°	50	46
65°	14	14
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750769

CATALOG NUMBER: LD4D60D010-EU4DR3555659035-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	15648.7
2.5°	15554.9
5°	15222.9
7.5°	14560.6
10°	13563.0
12.5°	12158.3
15°	10325.2
17.5°	8083.4
20°	5697.3
22.5°	3632.9
25°	2137.8
27.5°	1208.4
30°	762.1
32.5°	535.1
35°	395.1
37.5°	305.5
40°	241.5
42.5°	186.0
45°	135.7
47.5°	101.6
50°	78.5
52.5°	62.3
55°	49.5
57.5°	40.1
60°	31.6
62.5°	23.0
65°	14.5
67.5°	5.1
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)