

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750922

Luminaire Tested: LD4D60D010-EU4DR4555659035-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR4555659035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6227.3 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750922

CATALOG NUMBER: LD4D60D010-EU4DR4555659035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P750922

CATALOG NUMBER: LD4D60D010-EU4DR4555659035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1202611
5°	1168368
10°	1117817
15°	1023035
20°	811619
25°	506709
30°	279288
35°	125406
40°	49393
45°	23270
50°	11032
55°	5772
60°	2841
65°	672
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23270 cd/sqm



TEST NUMBER: P750922

CATALOG NUMBER: LD4D60D010-EU4DR4555659035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1000.9	16.1
10°-20°	2463.4	39.6
20°-30°	1950.8	31.3
30°-40°	649.6	10.4
40°-50°	128.9	2.1
50°-60°	29.3	0.5
60°-70°	4.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5415.1	87.0
0°-40°	6064.7	97.4
0°-60°	6222.9	99.9
0°-90°	6227.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6227.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11007	
5°	10653	###
15°	9044	2463
25°	4203	1951
35°	940	650
45°	151	129
55°	30	29
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750922

CATALOG NUMBER: LD4D60D010-EU4DR4555659035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	11006.8
2.5°	10935.0
5°	10652.7
7.5°	10419.9
10°	10075.3
12.5°	9616.5
15°	9044.2
17.5°	8183.7
20°	6980.3
22.5°	5546.7
25°	4203.1
27.5°	3077.7
30°	2213.7
32.5°	1505.5
35°	940.2
37.5°	557.5
40°	346.3
42.5°	227.7
45°	150.6
47.5°	97.0
50°	64.9
52.5°	43.3
55°	30.3
57.5°	19.9
60°	13.0
62.5°	6.9
65°	2.6
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)