

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P#

Luminaire Tested: LDSQRT3D17R129030DE010 3LSQPHUSR1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: LDSQRT3D17R129030DE010 3LSQPHUSR1MB
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , 3LSQPHUSR1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1386.0 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.22
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P#
CATALOG NUMBER: LDSQRT3D17R129030DE010 3LSQPHUSR1MB

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D17R129030DE010 3LSQPHUSR1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	116	114	113	111	114	112	111	109	108	107	106		104	104	103		101	101	100		98
2	113	110	108	106	111	108	106	104	105	104	102		103	101	100		100	99	98		97
3	110	107	104	102	109	105	103	101	103	101	99		101	99	98		99	98	96		95
4	108	104	101	98	107	103	100	98	101	99	97		99	97	96		98	96	95		94
5	106	102	98	96	105	101	98	96	99	97	95		98	96	94		97	95	93		92
6	104	99	96	94	103	99	96	94	98	95	93		96	94	93		95	93	92		91
7	102	98	94	92	101	97	94	92	96	93	92		95	93	91		94	92	91		90
8	101	96	93	91	100	95	93	90	95	92	90		94	92	90		93	91	90		89
9	99	94	91	89	98	94	91	89	93	91	89		93	90	89		92	90	88		88
10	98	93	90	88	97	93	90	88	92	90	88		91	89	88		91	89	87		87

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3516631
5°	2272203
10°	641108
15°	181258
20°	75803
25°	33559
30°	17142
35°	9062
40°	3867
45°	1047
50°	1152
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 50°

Luminance: 1152 cd/sqm

TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D17R129030DE010 3LSQPHUSR1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	926.0	66.8
10°-20°	336.0	24.2
20°-30°	90.0	6.5
30°-40°	28.3	2.0
40°-50°	5.3	0.4
50°-60°	0.5	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1352.0	97.5
0°-40°	1380.3	99.6
0°-60°	1386.0	100.0
0°-90°	1386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1386.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20419	
5°	13143	926
15°	1017	336
25°	177	90
35°	43	28
45°	4	5
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P#

CATALOG NUMBER: LDSQRT3D17R129030DE010 3LSQPHUSR1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	20419.1
1°	20074.4
2°	19105.2
3°	17446.7
4°	15387.5
5°	13143.2
6°	10804.0
7°	8710.4
8°	6703.0
9°	4988.5
10°	3666.0
11°	2701.0
12°	2033.3
13°	1576.7
14°	1249.3
15°	1016.6
17.5°	646.2
20°	413.6
22.5°	267.1
25°	176.6
27.5°	120.6
30°	86.2
32.5°	60.3
35°	43.1
37.5°	30.2
40°	17.2
42.5°	8.6
45°	4.3
47.5°	4.3
50°	4.3
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P#
CATALOG NUMBER: LDSQRT3D17R129030DE010 3LSQPHUSR1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)