

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751234

Luminaire Tested: LD4D60D010-EU4DR6555659035-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5327.7 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751234

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P751234

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	573127
5°	573595
10°	593784
15°	594770
20°	547587
25°	466575
30°	357181
35°	252347
40°	148948
45°	60463
50°	21927
55°	12210
60°	7015
65°	3852
70°	4057
75°	3166
80°	3272
85°	2758

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 60463 cd/sqm



TEST NUMBER: P751234

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	505.1	9.5
10°-20°	1457.0	27.3
20°-30°	1748.1	32.8
30°-40°	1174.8	22.1
40°-50°	351.7	6.6
50°-60°	62.1	1.2
60°-70°	17.7	0.3
70°-80°	8.7	0.2
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3710.1	69.6
0°-40°	4884.9	91.7
0°-60°	5298.6	99.5
0°-90°	5327.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5327.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5246	
5°	5230	505
15°	5258	1457
25°	3870	1748
35°	1892	1175
45°	391	352
55°	64	62
65°	15	18
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P751234

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	5245.5
2.5°	5267.8
5°	5229.8
7.5°	5308.8
10°	5352.0
12.5°	5341.6
15°	5258.1
17.5°	5053.9
20°	4709.5
22.5°	4304.0
25°	3870.2
27.5°	3380.4
30°	2831.1
32.5°	2333.1
35°	1891.9
37.5°	1455.8
40°	1044.3
42.5°	682.1
45°	391.3
47.5°	207.2
50°	129.0
52.5°	89.4
55°	64.1
57.5°	46.2
60°	32.1
62.5°	20.9
65°	14.9
67.5°	13.4
70°	12.7
72.5°	9.7
75°	7.5
77.5°	6.7
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)