

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751239

Luminaire Tested: LD4D60D010-EU4DR6555659035-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P751239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5888.5 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751239

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P751239

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	312262
5°	311473
10°	311208
15°	301613
20°	274582
25°	239278
30°	199012
35°	157690
40°	113812
45°	71899
50°	37480
55°	19917
60°	10466
65°	5749
70°	2408
75°	2663
80°	1850
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 71899 cd/sqm



TEST NUMBER: P751239

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	505.6	8.6
10°-20°	1384.6	23.5
20°-30°	1692.4	28.7
30°-40°	1373.2	23.3
40°-50°	684.3	11.6
50°-60°	190.9	3.2
60°-70°	43.4	0.7
70°-80°	11.3	0.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3582.6	60.8
0°-40°	4955.8	84.2
0°-60°	5830.9	99.0
0°-90°	5888.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5888.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5347	
5°	5313	506
15°	4988	1385
25°	3713	1692
35°	2212	1373
45°	870	684
55°	196	191
65°	42	43
75°	12	11
85°	2	3
90°	0	



TEST NUMBER: P751239

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5346.6
2.5°	5342.6
5°	5312.8
7.5°	5295.5
10°	5247.6
12.5°	5150.1
15°	4988.3
17.5°	4735.3
20°	4417.9
22.5°	4075.3
25°	3713.1
27.5°	3325.8
30°	2951.0
32.5°	2581.0
35°	2211.7
37.5°	1843.2
40°	1492.8
42.5°	1164.4
45°	870.5
47.5°	606.5
50°	412.5
52.5°	284.4
55°	195.6
57.5°	132.0
60°	89.6
62.5°	62.1
65°	41.6
67.5°	21.2
70°	14.1
72.5°	13.4
75°	11.8
77.5°	7.9
80°	5.5
82.5°	3.9
85°	2.4
87.5°	1.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)