

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P746558

Luminaire Tested: LD4D30D010-EU4DR6520359035-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P746558
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR6520359035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2607.7 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P746558
CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P746558

CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138289
5°	137938
10°	137819
15°	133571
20°	121601
25°	105968
30°	88136
35°	69836
40°	50403
45°	31841
50°	16600
55°	8818
60°	4626
65°	2543
70°	1059
75°	1173
80°	841
85°	670

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 31841 cd/sqm



TEST NUMBER: P746558

CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.9	8.6
10°-20°	613.2	23.5
20°-30°	749.5	28.7
30°-40°	608.1	23.3
40°-50°	303.0	11.6
50°-60°	84.5	3.2
60°-70°	19.2	0.7
70°-80°	5.0	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1586.6	60.8
0°-40°	2194.7	84.2
0°-60°	2582.3	99.0
0°-90°	2607.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2607.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2368	
5°	2353	224
15°	2209	613
25°	1644	750
35°	980	608
45°	386	303
55°	87	84
65°	18	19
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P746558

CATALOG NUMBER: LD4D30D010-EU4DR6520359035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2367.8
2.5°	2366.1
5°	2352.8
7.5°	2345.2
10°	2323.9
12.5°	2280.8
15°	2209.1
17.5°	2097.1
20°	1956.5
22.5°	1804.8
25°	1644.4
27.5°	1472.9
30°	1306.9
32.5°	1143.0
35°	979.5
37.5°	816.3
40°	661.1
42.5°	515.7
45°	385.5
47.5°	268.6
50°	182.7
52.5°	125.9
55°	86.6
57.5°	58.4
60°	39.6
62.5°	27.5
65°	18.4
67.5°	9.4
70°	6.2
72.5°	5.9
75°	5.2
77.5°	3.5
80°	2.5
82.5°	1.7
85°	1.0
87.5°	0.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)