

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750654

Luminaire Tested: LD4D60D010-EU4DR3055659024-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3055659024-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5564.6 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750654

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P750654

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1369583	1369583	1369583
5°	1330266	1328713	1330335
10°	1152215	1144092	1151943
15°	751760	747726	743962
20°	373817	387844	373312
25°	188304	212340	184444
30°	75392	82145	65688
35°	34966	33490	28070
40°	15098	16767	14219
45°	10652	13217	10749
50°	3656	9622	3870
55°	2108	3990	2229
60°	1485	1745	1485
65°	960	960	960
70°	582	403	582
75°	0	266	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 13217 cd/sqm



TEST NUMBER: P750654

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1573.4	28.3
10°-20°	2534.0	45.5
20°-30°	1095.0	19.7
30°-40°	249.6	4.5
40°-50°	85.7	1.5
50°-60°	20.9	0.4
60°-70°	5.4	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5202.4	93.5
0°-40°	5452.0	98.0
0°-60°	5558.6	99.9
0°-90°	5564.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5564.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	17893	17893	17893	17893	17893	
5°	17313	17296	17293	17329	17314	1575
15°	9487	9372	9436	9405	9388	2540
25°	2230	2314	2514	2255	2184	1067
35°	374	382	358	356	300	254
45°	98	122	122	122	99	70
55°	16	17	30	18	17	15
65°	5	5	5	5	5	5
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P750654

CATALOG NUMBER: LD4D60D010-EU4DR3055659024-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	17892.9	17892.9	17892.9	17892.9	17892.9
2.5°	17774.3	17762.0	17769.1	17777.9	17781.4
5°	17313.1	17296.5	17292.9	17329.0	17314.0
7.5°	16382.8	16359.1	16323.1	16404.8	16481.2
10°	14824.4	14798.0	14719.9	14758.5	14820.9
12.5°	12523.7	12438.4	12436.7	12559.7	12543.0
15°	9486.7	9372.5	9435.8	9405.0	9388.3
17.5°	6379.5	6335.6	6420.0	6394.5	6284.7
20°	4589.2	4600.6	4761.4	4680.6	4583.0
22.5°	3348.8	3390.1	3580.7	3372.5	3296.1
25°	2229.6	2313.9	2514.2	2255.1	2183.9
27.5°	1371.3	1410.0	1612.9	1353.7	1315.1
30°	853.0	833.7	929.4	797.7	743.2
32.5°	559.6	535.0	565.7	507.8	463.8
35°	374.2	382.1	358.4	355.8	300.4
37.5°	233.7	268.8	237.2	253.0	193.3
40°	151.1	195.0	167.8	185.4	142.3
42.5°	123.9	150.2	137.9	146.7	126.5
45°	98.4	122.1	122.1	122.1	99.3
47.5°	54.5	81.7	104.5	83.5	58.0
50°	30.7	41.3	80.8	43.0	32.5
52.5°	21.1	23.7	55.3	24.6	22.0
55°	15.8	16.7	29.9	17.6	16.7
57.5°	12.3	13.2	15.8	13.2	12.3
60°	9.7	9.7	11.4	10.5	9.7
62.5°	7.0	7.0	7.9	7.0	7.0
65°	5.3	5.3	5.3	5.3	5.3
67.5°	2.6	3.5	3.5	3.5	3.5
70°	2.6	1.8	1.8	1.8	2.6
72.5°	1.8	0.9	0.9	0.9	0.9
75°	0.0	0.0	0.9	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180° - - 45°-225° - - - 90°-270°







(END OF REPORT)