

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751278

Luminaire Tested: LD4D60D010-EU4DR7055659024-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751278
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR7055659024-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5751.9 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751278

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P751278

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	496044
5°	494802
10°	493733
15°	493589
20°	488765
25°	459137
30°	409312
35°	326348
40°	216697
45°	129548
50°	67159
55°	35298
60°	12478
65°	207
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 129548 cd/sqm



TEST NUMBER: P751278

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	429.0	7.5
10°-20°	1230.5	21.4
20°-30°	1735.8	30.2
30°-40°	1498.5	26.1
40°-50°	671.0	11.7
50°-60°	175.7	3.1
60°-70°	11.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3395.3	59.0
0°-40°	4893.8	85.1
0°-60°	5740.5	99.8
0°-90°	5751.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5751.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4540	
5°	4511	429
15°	4364	1230
25°	3808	1736
35°	2447	1498
45°	838	671
55°	185	176
65°	1	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751278

CATALOG NUMBER: LD4D60D010-EU4DR7055659024-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	4540.0
2.5°	4535.1
5°	4511.4
7.5°	4491.8
10°	4450.2
12.5°	4412.6
15°	4363.6
17.5°	4307.3
20°	4203.6
22.5°	4033.0
25°	3808.5
27.5°	3548.0
30°	3244.3
32.5°	2872.9
35°	2446.7
37.5°	1976.5
40°	1519.3
42.5°	1154.4
45°	838.4
47.5°	578.0
50°	395.1
52.5°	272.7
55°	185.3
57.5°	111.8
60°	57.1
62.5°	18.0
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)