

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751250

Luminaire Tested: LD4D60D010-EU4DR6555659040-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P751250
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659040-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5450.3 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751250

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P751250

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	289023
5°	288298
10°	288050
15°	279169
20°	254152
25°	221473
30°	184203
35°	145954
40°	105342
45°	66555
50°	34690
55°	18440
60°	9683
65°	5321
70°	2237
75°	2460
80°	1715
85°	1474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 66555 cd/sqm



TEST NUMBER: P751250

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	468.0	8.6
10°-20°	1281.5	23.5
20°-30°	1566.5	28.7
30°-40°	1271.0	23.3
40°-50°	633.4	11.6
50°-60°	176.7	3.2
60°-70°	40.1	0.7
70°-80°	10.5	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3316.0	60.8
0°-40°	4587.0	84.2
0°-60°	5397.1	99.0
0°-90°	5450.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5450.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4949	
5°	4918	468
15°	4617	1282
25°	3437	1566
35°	2047	1271
45°	806	633
55°	181	177
65°	38	40
75°	11	10
85°	2	3
90°	0	



TEST NUMBER: P751250

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4948.7
2.5°	4945.1
5°	4917.5
7.5°	4901.5
10°	4857.1
12.5°	4766.9
15°	4617.1
17.5°	4383.0
20°	4089.2
22.5°	3772.1
25°	3436.8
27.5°	3078.3
30°	2731.4
32.5°	2388.9
35°	2047.1
37.5°	1706.1
40°	1381.7
42.5°	1077.7
45°	805.8
47.5°	561.4
50°	381.8
52.5°	263.3
55°	181.1
57.5°	122.2
60°	82.9
62.5°	57.5
65°	38.5
67.5°	19.6
70°	13.1
72.5°	12.4
75°	10.9
77.5°	7.3
80°	5.1
82.5°	3.6
85°	2.2
87.5°	1.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)