

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750975

Luminaire Tested: LD4D60D010-EU4DR5055659027-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR5055659027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6361.3 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750975

CATALOG NUMBER: LD4D60D010-EU4DR5055659027-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P750975

CATALOG NUMBER: LD4D60D010-EU4DR5055659027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107		112	110	108	106		106	104	102			102	101	99			95
2	109	105	101	98		107	103	100	97		100	98	95			97	95	93			90
3	105	99	95	91		103	98	94	90		95	92	89			93	90	88			85
4	100	94	89	85		99	93	88	85		90	87	84			89	85	83			80
5	96	89	84	80		95	88	83	79		86	82	79			85	81	78			76
6	92	84	79	75		91	83	79	75		82	78	74			81	77	74			72
7	88	80	75	71		87	79	74	71		78	74	71			77	73	70			69
8	85	76	71	67		84	76	71	67		75	70	67			74	70	67			65
9	81	73	68	64		80	72	67	64		71	67	64			71	67	64			62
10	78	70	64	61		77	69	64	61		68	64	61			68	64	61			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1119890
5°	1108155
10°	1089903
15°	992438
20°	825828
25°	586215
30°	310286
35°	126447
40°	46954
45°	21493
50°	8805
55°	4610
60°	2273
65°	672
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21493 cd/sqm



TEST NUMBER: P750975

CATALOG NUMBER: LD4D60D010-EU4DR5055659027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	955.0	15.0
10°-20°	2413.5	37.9
20°-30°	2168.0	34.1
30°-40°	678.8	10.7
40°-50°	118.8	1.9
50°-60°	23.7	0.4
60°-70°	3.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5536.4	87.0
0°-40°	6215.2	97.7
0°-60°	6357.7	99.9
0°-90°	6361.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6361.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10250	
5°	10104	955
15°	8774	2413
25°	4863	2168
35°	948	679
45°	139	119
55°	24	24
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750975

CATALOG NUMBER: LD4D60D010-EU4DR5055659027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10249.7
2.5°	10198.7
5°	10103.7
7.5°	9958.5
10°	9823.7
12.5°	9391.6
15°	8773.7
17.5°	7989.1
20°	7102.5
22.5°	6076.7
25°	4862.6
27.5°	3575.0
30°	2459.4
32.5°	1601.3
35°	948.0
37.5°	544.4
40°	329.2
42.5°	214.3
45°	139.1
47.5°	84.7
50°	51.8
52.5°	35.4
55°	24.2
57.5°	16.4
60°	10.4
62.5°	6.0
65°	2.6
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)