

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750641

Luminaire Tested: LD4D60D010-EU4DR2555659050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750641
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR2555659050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6330.1 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750641

CATALOG NUMBER: LD4D60D010-EU4DR2555659050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P750641

CATALOG NUMBER: LD4D60D010-EU4DR2555659050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	94	94	92
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	90	90	89
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	87	87	85
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	83	83	82
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	80	80	79
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	78	78	77
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	75	75	74
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	73	73	72
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	70	70	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2623198
5°	2443179
10°	1742789
15°	1026429
20°	638664
25°	350504
30°	160291
35°	60702
40°	27485
45°	16533
50°	6867
55°	4419
60°	3081
65°	2094
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16533 cd/sqm



TEST NUMBER: P750641

CATALOG NUMBER: LD4D60D010-EU4DR2555659050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1914.4	30.2
10°-20°	2593.0	41.0
20°-30°	1372.2	21.7
30°-40°	338.7	5.4
40°-50°	82.6	1.3
50°-60°	21.8	0.3
60°-70°	7.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5879.5	92.9
0°-40°	6218.3	98.2
0°-60°	6322.7	99.9
0°-90°	6330.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6330.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	24009	
5°	22276	###
15°	9074	2593
25°	2907	1372
35°	455	339
45°	107	83
55°	23	22
65°	8	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750641

CATALOG NUMBER: LD4D60D010-EU4DR2555659050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	24008.6
2.5°	23614.0
5°	22275.9
7.5°	19587.5
10°	15708.4
12.5°	11874.6
15°	9074.2
17.5°	7072.1
20°	5492.8
22.5°	4119.3
25°	2907.4
27.5°	1949.7
30°	1270.5
32.5°	773.0
35°	455.1
37.5°	278.5
40°	192.7
42.5°	147.3
45°	107.0
47.5°	64.6
50°	40.4
52.5°	29.3
55°	23.2
57.5°	18.2
60°	14.1
62.5°	11.1
65°	8.1
67.5°	3.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)