

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751214

Luminaire Tested: LD4D60D010-EU4DR6555659027-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P751214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5118.7 lumens
Efficiency: N/A
Efficacy: 79.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751214

CATALOG NUMBER: LD4D60D010-EU4DR6555659027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751214

CATALOG NUMBER: LD4D60D010-EU4DR6555659027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	271438
5°	270757
10°	270525
15°	262185
20°	238689
25°	207998
30°	172994
35°	137077
40°	98930
45°	62500
50°	32583
55°	17320
60°	9099
65°	5003
70°	2100
75°	2302
80°	1614
85°	1340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 62500 cd/sqm



TEST NUMBER: P751214

CATALOG NUMBER: LD4D60D010-EU4DR6555659027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.5	8.6
10°-20°	1203.6	23.5
20°-30°	1471.2	28.7
30°-40°	1193.7	23.3
40°-50°	594.8	11.6
50°-60°	165.9	3.2
60°-70°	37.7	0.7
70°-80°	9.8	0.2
80°-90°	2.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3114.3	60.8
0°-40°	4307.9	84.2
0°-60°	5068.7	99.0
0°-90°	5118.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5118.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4648	
5°	4618	440
15°	4336	1204
25°	3228	1471
35°	1923	1194
45°	757	595
55°	170	166
65°	36	38
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P751214

CATALOG NUMBER: LD4D60D010-EU4DR6555659027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4647.6
2.5°	4644.2
5°	4618.3
7.5°	4603.2
10°	4561.6
12.5°	4476.9
15°	4336.2
17.5°	4116.3
20°	3840.4
22.5°	3542.6
25°	3227.7
27.5°	2891.0
30°	2565.2
32.5°	2243.6
35°	1922.6
37.5°	1602.3
40°	1297.6
42.5°	1012.2
45°	756.7
47.5°	527.3
50°	358.6
52.5°	247.2
55°	170.1
57.5°	114.7
60°	77.9
62.5°	54.0
65°	36.2
67.5°	18.4
70°	12.3
72.5°	11.6
75°	10.2
77.5°	6.8
80°	4.8
82.5°	3.4
85°	2.0
87.5°	1.4
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)