

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751291

Luminaire Tested: LD4D60D010-EU4DR7055659027-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR7055659027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6515.7 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751291

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P751291

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	561906
5°	560499
10°	559280
15°	559128
20°	553668
25°	520102
30°	463663
35°	369684
40°	245466
45°	146761
50°	76083
55°	39984
60°	14138
65°	233
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 146761 cd/sqm



TEST NUMBER: P751291

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	486.0	7.5
10°-20°	1393.8	21.4
20°-30°	1966.3	30.2
30°-40°	1697.4	26.1
40°-50°	760.2	11.7
50°-60°	199.0	3.1
60°-70°	12.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3846.2	59.0
0°-40°	5543.6	85.1
0°-60°	6502.8	99.8
0°-90°	6515.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6515.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5143	
5°	5110	486
15°	4943	1394
25°	4314	1966
35°	2772	1697
45°	950	760
55°	210	199
65°	1	13
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751291

CATALOG NUMBER: LD4D60D010-EU4DR7055659027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5142.8
2.5°	5137.2
5°	5110.4
7.5°	5088.2
10°	5041.0
12.5°	4998.5
15°	4943.0
17.5°	4879.2
20°	4761.8
22.5°	4568.5
25°	4314.2
27.5°	4019.2
30°	3675.1
32.5°	3254.3
35°	2771.6
37.5°	2238.9
40°	1721.0
42.5°	1307.7
45°	949.8
47.5°	654.8
50°	447.6
52.5°	308.9
55°	209.9
57.5°	126.7
60°	64.7
62.5°	20.3
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)