

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750752

Luminaire Tested: LD4D60D010-EU4DR3555659030-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3555659030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4974.4 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750752

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P750752

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1495452
5°	1460320
10°	1316134
15°	1021531
20°	579399
25°	225415
30°	84088
35°	46097
40°	30123
45°	18341
50°	11678
55°	8248
60°	6031
65°	3283
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 18341 cd/sqm

TEST NUMBER: P750752

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1224.5	24.6
10°-20°	2390.8	48.1
20°-30°	975.1	19.6
30°-40°	233.3	4.7
40°-50°	97.2	2.0
50°-60°	40.3	0.8
60°-70°	12.6	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4590.5	92.3
0°-40°	4823.8	97.0
0°-60°	4961.3	99.7
0°-90°	4974.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4974.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13687	
5°	13315	###
15°	9031	2391
25°	1870	975
35°	346	233
45°	119	97
55°	43	40
65°	13	13
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750752

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	13687.0
2.5°	13604.9
5°	13314.6
7.5°	12735.3
10°	11862.8
12.5°	10634.2
15°	9030.9
17.5°	7070.0
20°	4983.1
22.5°	3177.5
25°	1869.8
27.5°	1056.9
30°	666.5
32.5°	468.0
35°	345.6
37.5°	267.2
40°	211.2
42.5°	162.7
45°	118.7
47.5°	88.8
50°	68.7
52.5°	54.5
55°	43.3
57.5°	35.1
60°	27.6
62.5°	20.2
65°	12.7
67.5°	4.5
70°	0.7
72.5°	0.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)