

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750756

Luminaire Tested: LD4D60D010-EU4DR3555659030-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3555659030-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5628.0 lumens
Efficiency: N/A
Efficacy: 87.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750756

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P750756

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1691968
5°	1652213
10°	1489088
15°	1155764
20°	655535
25°	255036
30°	95140
35°	52153
40°	34089
45°	20752
50°	13207
55°	9334
60°	6818
65°	3723
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20752 cd/sqm

TEST NUMBER: P750756

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1385.5	24.6
10°-20°	2705.0	48.1
20°-30°	1103.2	19.6
30°-40°	264.0	4.7
40°-50°	110.0	2.0
50°-60°	45.5	0.8
60°-70°	14.3	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5193.7	92.3
0°-40°	5457.7	97.0
0°-60°	5613.3	99.7
0°-90°	5628.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5628.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15486	
5°	15064	###
15°	10218	2705
25°	2116	1103
35°	391	264
45°	134	110
55°	49	46
65°	14	14
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750756

CATALOG NUMBER: LD4D60D010-EU4DR3555659030-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	15485.6
2.5°	15392.7
5°	15064.2
7.5°	14408.9
10°	13421.7
12.5°	12031.6
15°	10217.6
17.5°	7999.1
20°	5637.9
22.5°	3595.0
25°	2115.5
27.5°	1195.8
30°	754.1
32.5°	529.5
35°	391.0
37.5°	302.3
40°	239.0
42.5°	184.1
45°	134.3
47.5°	100.5
50°	77.7
52.5°	61.6
55°	49.0
57.5°	39.7
60°	31.2
62.5°	22.8
65°	14.4
67.5°	5.1
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)