

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750835

Luminaire Tested: LD4D60D010-EU4DR4055659030-4LBS1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P750835  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D60D010-EU4DR4055659030-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6611.7 lumens  
Efficiency: N/A  
Efficacy: 102.7 lumens/watt  
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 64.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P750835

CATALOG NUMBER: LD4D60D010-EU4DR4055659030-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P750835

CATALOG NUMBER: LD4D60D010-EU4DR4055659030-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 |  | 106 | 105 | 103 |  |  | 103 | 101 | 100 |  |  | 99  |
| 2   | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99  |  | 102 | 99  | 97  |  |  | 99  | 97  | 95  |  |  | 96  |
| 3   | 106 | 101 | 97  | 94  | 104 | 100 | 96  | 93  |  | 97  | 94  | 92  |  |  | 95  | 93  | 90  |  |  | 93  |
| 4   | 102 | 97  | 92  | 89  | 101 | 95  | 91  | 88  |  | 93  | 90  | 87  |  |  | 92  | 89  | 86  |  |  | 90  |
| 5   | 99  | 92  | 88  | 84  | 97  | 91  | 87  | 84  |  | 90  | 86  | 83  |  |  | 88  | 85  | 83  |  |  | 87  |
| 6   | 95  | 88  | 84  | 80  | 94  | 88  | 83  | 80  |  | 86  | 82  | 80  |  |  | 85  | 82  | 79  |  |  | 84  |
| 7   | 92  | 85  | 80  | 77  | 91  | 84  | 80  | 77  |  | 83  | 79  | 76  |  |  | 82  | 79  | 76  |  |  | 81  |
| 8   | 89  | 82  | 77  | 74  | 88  | 81  | 77  | 74  |  | 80  | 76  | 73  |  |  | 79  | 76  | 73  |  |  | 78  |
| 9   | 86  | 79  | 74  | 71  | 85  | 78  | 74  | 71  |  | 77  | 73  | 71  |  |  | 76  | 73  | 70  |  |  | 76  |
| 10  | 83  | 76  | 71  | 68  | 82  | 75  | 71  | 68  |  | 75  | 71  | 68  |  |  | 74  | 70  | 68  |  |  | 73  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1681916 |
| 5°  | 1673743 |
| 10° | 1582050 |
| 15° | 1344949 |
| 20° | 916684  |
| 25° | 382476  |
| 30° | 120259  |
| 35° | 55901   |
| 40° | 30908   |
| 45° | 14169   |
| 50° | 6884    |
| 55° | 3772    |
| 60° | 1967    |
| 65° | 698     |
| 70° | 288     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14169 cd/sqm



TEST NUMBER: P750835

CATALOG NUMBER: LD4D60D010-EU4DR4055659030-4LBS1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1424.9 | 21.6      |
| 10°-20°   | 3192.3 | 48.3      |
| 20°-30°   | 1597.9 | 24.2      |
| 30°-40°   | 292.9  | 4.4       |
| 40°-50°   | 80.8   | 1.2       |
| 50°-60°   | 19.0   | 0.3       |
| 60°-70°   | 3.6    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 6215.2 | 94.0      |
| 0°-40°    | 6508.1 | 98.4      |
| 0°-60°    | 6607.9 | 99.9      |
| 0°-90°    | 6611.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 6611.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 15394 |      |
| 5°  | 15260 | ###  |
| 15° | 11890 | 3192 |
| 25° | 3173  | 1598 |
| 35° | 419   | 293  |
| 45° | 92    | 81   |
| 55° | 20    | 19   |
| 65° | 3     | 4    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P750835

CATALOG NUMBER: LD4D60D010-EU4DR4055659030-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 15393.6 |
| 2.5°  | 15371.1 |
| 5°    | 15260.5 |
| 7.5°  | 14908.0 |
| 10°   | 14259.6 |
| 12.5° | 13248.9 |
| 15°   | 11890.1 |
| 17.5° | 10123.0 |
| 20°   | 7883.9  |
| 22.5° | 5374.9  |
| 25°   | 3172.6  |
| 27.5° | 1677.1  |
| 30°   | 953.2   |
| 32.5° | 616.0   |
| 35°   | 419.1   |
| 37.5° | 299.5   |
| 40°   | 216.7   |
| 42.5° | 148.4   |
| 45°   | 91.7    |
| 47.5° | 58.5    |
| 50°   | 40.5    |
| 52.5° | 28.8    |
| 55°   | 19.8    |
| 57.5° | 12.6    |
| 60°   | 9.0     |
| 62.5° | 5.4     |
| 65°   | 2.7     |
| 67.5° | 1.8     |
| 70°   | 0.9     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)