

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751718

Luminaire Tested: LD4D65D010-EU4DR4555659040-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR4555659040-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7106.9 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751718

CATALOG NUMBER: LD4D65D010-EU4DR4555659040-4LBS1B

Luminous Intensity Polar Plot



TEST NUMBER: P751718

CATALOG NUMBER: LD4D65D010-EU4DR4555659040-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1372479
5°	1333412
10°	1275716
15°	1167540
20°	926265
25°	578283
30°	318727
35°	143120
40°	56367
45°	26562
50°	12595
55°	6591
60°	3234
65°	776
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26562 cd/sqm



TEST NUMBER: P751718

CATALOG NUMBER: LD4D65D010-EU4DR4555659040-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1142.3	16.1
10°-20°	2811.4	39.6
20°-30°	2226.3	31.3
30°-40°	741.4	10.4
40°-50°	147.1	2.1
50°-60°	33.4	0.5
60°-70°	4.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6180.0	87.0
0°-40°	6921.4	97.4
0°-60°	7101.9	99.9
0°-90°	7106.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7106.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12562	
5°	12158	###
15°	10322	2811
25°	4797	2226
35°	1073	741
45°	172	147
55°	35	33
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751718

CATALOG NUMBER: LD4D65D010-EU4DR4555659040-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	12561.5
2.5°	12479.5
5°	12157.5
7.5°	11891.7
10°	11498.5
12.5°	10974.8
15°	10321.7
17.5°	9339.7
20°	7966.3
22.5°	6330.2
25°	4796.8
27.5°	3512.4
30°	2526.3
32.5°	1718.1
35°	1073.0
37.5°	636.3
40°	395.2
42.5°	259.8
45°	171.9
47.5°	110.7
50°	74.1
52.5°	49.4
55°	34.6
57.5°	22.7
60°	14.8
62.5°	7.9
65°	3.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)