

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751223

Luminaire Tested: LD4D60D010-EU4DR6555659030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751223
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4548.8 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751223

CATALOG NUMBER: LD4D60D010-EU4DR6555659030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751223

CATALOG NUMBER: LD4D60D010-EU4DR6555659030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	489335
5°	489735
10°	506980
15°	507819
20°	467533
25°	398353
30°	304962
35°	215453
40°	127169
45°	51624
50°	18715
55°	10420
60°	5987
65°	3283
70°	3450
75°	2702
80°	2831
85°	2382

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 51624 cd/sqm



TEST NUMBER: P751223

CATALOG NUMBER: LD4D60D010-EU4DR6555659030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	431.2	9.5
10°-20°	1244.0	27.3
20°-30°	1492.5	32.8
30°-40°	1003.0	22.0
40°-50°	300.2	6.6
50°-60°	53.0	1.2
60°-70°	15.1	0.3
70°-80°	7.4	0.2
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3167.7	69.6
0°-40°	4170.7	91.7
0°-60°	4523.9	99.5
0°-90°	4548.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4548.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4479	
5°	4465	431
15°	4489	1244
25°	3304	1493
35°	1615	1003
45°	334	300
55°	55	53
65°	13	15
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P751223

CATALOG NUMBER: LD4D60D010-EU4DR6555659030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4478.6
2.5°	4497.7
5°	4465.2
7.5°	4532.7
10°	4569.6
12.5°	4560.7
15°	4489.4
17.5°	4315.0
20°	4021.0
22.5°	3674.7
25°	3304.3
27.5°	2886.2
30°	2417.2
32.5°	1992.0
35°	1615.3
37.5°	1242.9
40°	891.6
42.5°	582.3
45°	334.1
47.5°	176.9
50°	110.1
52.5°	76.4
55°	54.7
57.5°	39.5
60°	27.4
62.5°	17.8
65°	12.7
67.5°	11.5
70°	10.8
72.5°	8.3
75°	6.4
77.5°	5.7
80°	4.5
82.5°	3.2
85°	1.9
87.5°	1.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)