

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751226

Luminaire Tested: LD4D60D010-EU4DR6555659030-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P751226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5827.1 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751226

CATALOG NUMBER: LD4D60D010-EU4DR6555659030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P751226

CATALOG NUMBER: LD4D60D010-EU4DR6555659030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	309003
5°	308225
10°	307964
15°	298469
20°	271717
25°	236784
30°	196942
35°	156043
40°	112623
45°	71156
50°	37089
55°	19713
60°	10349
65°	5694
70°	2391
75°	2640
80°	1816
85°	1541

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 71156 cd/sqm



TEST NUMBER: P751226

CATALOG NUMBER: LD4D60D010-EU4DR6555659030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	500.3	8.6
10°-20°	1370.1	23.5
20°-30°	1674.8	28.7
30°-40°	1358.9	23.3
40°-50°	677.1	11.6
50°-60°	188.9	3.2
60°-70°	42.9	0.7
70°-80°	11.2	0.2
80°-90°	2.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3545.3	60.8
0°-40°	4904.1	84.2
0°-60°	5770.1	99.0
0°-90°	5827.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5827.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5291	
5°	5257	500
15°	4936	1370
25°	3674	1675
35°	2189	1359
45°	862	677
55°	194	189
65°	41	43
75°	12	11
85°	2	3
90°	0	



TEST NUMBER: P751226

CATALOG NUMBER: LD4D60D010-EU4DR6555659030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5290.8
2.5°	5286.9
5°	5257.4
7.5°	5240.3
10°	5192.9
12.5°	5096.5
15°	4936.3
17.5°	4685.9
20°	4371.8
22.5°	4032.9
25°	3674.4
27.5°	3291.1
30°	2920.3
32.5°	2554.1
35°	2188.6
37.5°	1824.0
40°	1477.2
42.5°	1152.2
45°	861.5
47.5°	600.2
50°	408.2
52.5°	281.5
55°	193.6
57.5°	130.6
60°	88.6
62.5°	61.4
65°	41.2
67.5°	21.0
70°	14.0
72.5°	13.2
75°	11.7
77.5°	7.8
80°	5.4
82.5°	3.9
85°	2.3
87.5°	1.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)