

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752364

Luminaire Tested: LD4D70BD010-EU4DR4070959024-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR4070959024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5407.5 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752364

CATALOG NUMBER: LD4D70BD010-EU4DR4070959024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P752364

CATALOG NUMBER: LD4D70BD010-EU4DR4070959024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1375593
5°	1368903
10°	1293911
15°	1099987
20°	749727
25°	312818
30°	98357
35°	45710
40°	25288
45°	11589
50°	5626
55°	3086
60°	1617
65°	569
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11589 cd/sqm



TEST NUMBER: P752364

CATALOG NUMBER: LD4D70BD010-EU4DR4070959024-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1165.4	21.6
10°-20°	2610.9	48.3
20°-30°	1306.9	24.2
30°-40°	239.6	4.4
40°-50°	66.1	1.2
50°-60°	15.5	0.3
60°-70°	3.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5083.2	94.0
0°-40°	5322.8	98.4
0°-60°	5404.4	99.9
0°-90°	5407.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5407.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12590	
5°	12481	###
15°	9724	2611
25°	2595	1307
35°	343	240
45°	75	66
55°	16	16
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752364

CATALOG NUMBER: LD4D70BD010-EU4DR4070959024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	12590.0
2.5°	12571.6
5°	12481.1
7.5°	12192.8
10°	11662.5
12.5°	10835.8
15°	9724.5
17.5°	8279.3
20°	6448.0
22.5°	4396.0
25°	2594.8
27.5°	1371.7
30°	779.6
32.5°	503.8
35°	342.7
37.5°	244.9
40°	177.3
42.5°	121.4
45°	75.0
47.5°	47.8
50°	33.1
52.5°	23.5
55°	16.2
57.5°	10.3
60°	7.4
62.5°	4.4
65°	2.2
67.5°	1.5
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)