

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751304

Luminaire Tested: LD4D60D010-EU4DR7055659030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR7055659030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6712.7 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751304

CATALOG NUMBER: LD4D60D010-EU4DR7055659030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P751304

CATALOG NUMBER: LD4D60D010-EU4DR7055659030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105	111	108	106	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94	105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84	99	92	87	83		90	85	82		87	84	81		85	82	79
4	95	87	81	76	93	86	80	76		83	78	75		81	77	74		79	76	73
5	89	80	74	69	88	79	73	69		78	72	68		76	71	68		74	70	67
6	84	75	68	63	83	74	68	63		72	67	63		71	66	62		69	65	62
7	80	69	63	58	78	69	62	58		67	62	58		66	61	57		65	61	57
8	75	65	58	54	74	64	58	54		63	57	53		62	57	53		61	56	53
9	71	61	54	50	70	60	54	50		59	53	50		58	53	49		57	53	49
10	67	57	50	46	66	56	50	46		55	50	46		55	50	46		54	49	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	578885
5°	577433
10°	576188
15°	576027
20°	570400
25°	535811
30°	477680
35°	380861
40°	252883
45°	151196
50°	78378
55°	41203
60°	14575
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 151196 cd/sqm



TEST NUMBER: P751304

CATALOG NUMBER: LD4D60D010-EU4DR7055659030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	500.7	7.5
10°-20°	1436.0	21.4
20°-30°	2025.7	30.2
30°-40°	1748.8	26.1
40°-50°	783.1	11.7
50°-60°	205.0	3.1
60°-70°	13.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3962.4	59.0
0°-40°	5711.1	85.1
0°-60°	6699.3	99.8
0°-90°	6712.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6712.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5298	
5°	5265	501
15°	5092	1436
25°	4444	2026
35°	2855	1749
45°	978	783
55°	216	205
65°	1	13
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751304

CATALOG NUMBER: LD4D60D010-EU4DR7055659030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5298.2
2.5°	5292.5
5°	5264.8
7.5°	5242.0
10°	5193.4
12.5°	5149.6
15°	5092.4
17.5°	5026.7
20°	4905.7
22.5°	4706.5
25°	4444.5
27.5°	4140.6
30°	3786.2
32.5°	3352.7
35°	2855.4
37.5°	2306.6
40°	1773.0
42.5°	1347.2
45°	978.5
47.5°	674.5
50°	461.1
52.5°	318.2
55°	216.3
57.5°	130.5
60°	66.7
62.5°	21.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)