

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750611

Luminaire Tested: LD4D60D010-EU4DR2555659035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR2555659035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5704.3 lumens
Efficiency: N/A
Efficacy: 88.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750611

CATALOG NUMBER: LD4D60D010-EU4DR2555659035-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P750611

CATALOG NUMBER: LD4D60D010-EU4DR2555659035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2363845
5°	2201624
10°	1570478
15°	924953
20°	575516
25°	315844
30°	144445
35°	54700
40°	24775
45°	14896
50°	6187
55°	3981
60°	2775
65°	1887
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14896 cd/sqm



TEST NUMBER: P750611

CATALOG NUMBER: LD4D60D010-EU4DR2555659035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1725.2	30.2
10°-20°	2336.6	41.0
20°-30°	1236.5	21.7
30°-40°	305.2	5.4
40°-50°	74.5	1.3
50°-60°	19.6	0.3
60°-70°	6.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5298.2	92.9
0°-40°	5603.5	98.2
0°-60°	5697.6	99.9
0°-90°	5704.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5704.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21635	
5°	20074	###
15°	8177	2337
25°	2620	1236
35°	410	305
45°	96	74
55°	21	20
65°	7	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750611

CATALOG NUMBER: LD4D60D010-EU4DR2555659035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	21634.9
2.5°	21279.4
5°	20073.5
7.5°	17651.0
10°	14155.3
12.5°	10700.6
15°	8177.1
17.5°	6372.9
20°	4949.7
22.5°	3712.1
25°	2619.9
27.5°	1756.9
30°	1144.9
32.5°	696.6
35°	410.1
37.5°	251.0
40°	173.7
42.5°	132.8
45°	96.4
47.5°	58.2
50°	36.4
52.5°	26.4
55°	20.9
57.5°	16.4
60°	12.7
62.5°	10.0
65°	7.3
67.5°	2.7
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)