

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750767

Luminaire Tested: LD4D60D010-EU4DR3555659035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750767
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3555659035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6097.8 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750767

CATALOG NUMBER: LD4D60D010-EU4DR3555659035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P750767

CATALOG NUMBER: LD4D60D010-EU4DR3555659035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108	112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101	108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94	105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89	101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85	98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81	94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78	91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74	88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72	86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69	83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1833188
5°	1790111
10°	1613370
15°	1252229
20°	710241
25°	276314
30°	103088
35°	56501
40°	36927
45°	22482
50°	14312
55°	10115
60°	7408
65°	4033
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22482 cd/sqm



TEST NUMBER: P750767

CATALOG NUMBER: LD4D60D010-EU4DR3555659035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1501.1	24.6
10°-20°	2930.8	48.1
20°-30°	1195.3	19.6
30°-40°	286.0	4.7
40°-50°	119.2	2.0
50°-60°	49.4	0.8
60°-70°	15.5	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5627.2	92.3
0°-40°	5913.2	97.0
0°-60°	6081.8	99.7
0°-90°	6097.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6097.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16778	
5°	16322	###
15°	11070	2931
25°	2292	1195
35°	424	286
45°	146	119
55°	53	49
65°	16	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750767

CATALOG NUMBER: LD4D60D010-EU4DR3555659035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	16778.1
2.5°	16677.4
5°	16321.5
7.5°	15611.5
10°	14541.9
12.5°	13035.8
15°	11070.4
17.5°	8666.7
20°	6108.4
22.5°	3895.1
25°	2292.0
27.5°	1295.6
30°	817.1
32.5°	573.7
35°	423.6
37.5°	327.6
40°	258.9
42.5°	199.5
45°	145.5
47.5°	108.9
50°	84.2
52.5°	66.8
55°	53.1
57.5°	43.0
60°	33.9
62.5°	24.7
65°	15.6
67.5°	5.5
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)