

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750844

Luminaire Tested: LD4D60D010-EU4DR4055659035-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR4055659035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6347.2 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750844

CATALOG NUMBER: LD4D60D010-EU4DR4055659035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P750844

CATALOG NUMBER: LD4D60D010-EU4DR4055659035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96		
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88		
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84		
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81		
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77		
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74		
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72		
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69		
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1614655
5°	1606806
10°	1518788
15°	1291163
20°	880023
25°	367177
30°	115452
35°	53660
40°	29681
45°	13613
50°	6595
55°	3619
60°	1879
65°	672
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13613 cd/sqm



TEST NUMBER: P750844

CATALOG NUMBER: LD4D60D010-EU4DR4055659035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1368.0	21.6
10°-20°	3064.6	48.3
20°-30°	1534.0	24.2
30°-40°	281.2	4.4
40°-50°	77.6	1.2
50°-60°	18.2	0.3
60°-70°	3.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5966.6	94.0
0°-40°	6247.8	98.4
0°-60°	6343.6	99.9
0°-90°	6347.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6347.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14778	
5°	14650	###
15°	11415	3065
25°	3046	1534
35°	402	281
45°	88	78
55°	19	18
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750844

CATALOG NUMBER: LD4D60D010-EU4DR4055659035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	14778.0
2.5°	14756.4
5°	14650.2
7.5°	14311.8
10°	13689.4
12.5°	12719.0
15°	11414.6
17.5°	9718.2
20°	7568.6
22.5°	5159.9
25°	3045.7
27.5°	1610.1
30°	915.1
32.5°	591.4
35°	402.3
37.5°	287.5
40°	208.1
42.5°	142.4
45°	88.1
47.5°	56.1
50°	38.8
52.5°	27.6
55°	19.0
57.5°	12.1
60°	8.6
62.5°	5.2
65°	2.6
67.5°	1.7
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)