

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750926

Luminaire Tested: LD4D60D010-EU4DR4555659035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750926
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR4555659035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6555.0 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750926

CATALOG NUMBER: LD4D60D010-EU4DR4555659035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P750926

CATALOG NUMBER: LD4D60D010-EU4DR4555659035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			98
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	91		103	98	94	91		95	92	89			93	90	88			91
4	100	94	89	85		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	83	80		86	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	77	75			80
7	89	81	75	72		87	80	75	72		79	74	71			78	74	71			77
8	85	77	72	68		84	76	71	68		75	71	68			74	70	67			73
9	82	73	68	65		81	73	68	65		72	68	65			71	67	64			71
10	79	70	65	62		78	70	65	62		69	65	62			68	64	61			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1265906
5°	1229865
10°	1176652
15°	1076878
20°	854338
25°	533375
30°	293986
35°	132009
40°	51989
45°	24507
50°	11610
55°	6077
60°	2994
65°	698
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24507 cd/sqm



TEST NUMBER: P750926

CATALOG NUMBER: LD4D60D010-EU4DR4555659035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1053.6	16.1
10°-20°	2593.0	39.6
20°-30°	2053.4	31.3
30°-40°	683.8	10.4
40°-50°	135.7	2.1
50°-60°	30.8	0.5
60°-70°	4.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5700.1	87.0
0°-40°	6383.9	97.4
0°-60°	6550.5	99.9
0°-90°	6555.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6555.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11586	
5°	11213	###
15°	9520	2593
25°	4424	2053
35°	990	684
45°	159	136
55°	32	31
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750926

CATALOG NUMBER: LD4D60D010-EU4DR4555659035-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	11586.1
2.5°	11510.5
5°	11213.4
7.5°	10968.3
10°	10605.6
12.5°	10122.6
15°	9520.2
17.5°	8614.4
20°	7347.7
22.5°	5838.6
25°	4424.3
27.5°	3239.6
30°	2330.2
32.5°	1584.7
35°	989.7
37.5°	586.9
40°	364.5
42.5°	239.7
45°	158.6
47.5°	102.1
50°	68.3
52.5°	45.6
55°	31.9
57.5°	21.0
60°	13.7
62.5°	7.3
65°	2.7
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)