

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751002

Luminaire Tested: LD4D60D010-EU4DR5055659035-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P751002
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR5055659035-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5998.9 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751002

CATALOG NUMBER: LD4D60D010-EU4DR5055659035-4LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P751002

CATALOG NUMBER: LD4D60D010-EU4DR5055659035-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1056082
5°	1045013
10°	1027795
15°	935891
20°	778772
25°	552809
30°	292598
35°	119244
40°	44287
45°	20273
50°	8312
55°	4343
60°	2142
65°	620
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20273 cd/sqm

TEST NUMBER: P751002

CATALOG NUMBER: LD4D60D010-EU4DR5055659035-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	900.6	15.0
10°-20°	2276.0	37.9
20°-30°	2044.4	34.1
30°-40°	640.1	10.7
40°-50°	112.1	1.9
50°-60°	22.3	0.4
60°-70°	3.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5221.0	87.0
0°-40°	5861.1	97.7
0°-60°	5995.5	99.9
0°-90°	5998.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5998.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9666	
5°	9528	901
15°	8274	2276
25°	4586	2044
35°	894	640
45°	131	112
55°	23	22
65°	2	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P751002

CATALOG NUMBER: LD4D60D010-EU4DR5055659035-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9665.7
2.5°	9617.6
5°	9528.0
7.5°	9391.1
10°	9263.9
12.5°	8856.5
15°	8273.8
17.5°	7533.9
20°	6697.8
22.5°	5730.5
25°	4585.5
27.5°	3371.3
30°	2319.2
32.5°	1510.0
35°	894.0
37.5°	513.4
40°	310.5
42.5°	202.1
45°	131.2
47.5°	79.9
50°	48.9
52.5°	33.4
55°	22.8
57.5°	15.5
60°	9.8
62.5°	5.7
65°	2.4
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)