

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751158

Luminaire Tested: LD4D60D010-EU4DR6055659035-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6055659035-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5521.7 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751158

CATALOG NUMBER: LD4D60D010-EU4DR6055659035-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751158

CATALOG NUMBER: LD4D60D010-EU4DR6055659035-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	95		105	101	97	94		97	94	92		94	92	90		92	90	88
3	102	96	90	86		100	94	89	86		91	88	84		89	86	83		87	84	82
4	97	89	84	80		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	78	73	69		77	72	68		75	71	68		74	70	67
7	84	75	69	65		83	74	68	64		73	68	64		72	67	64		71	67	63
8	80	71	65	61		79	70	65	61		69	64	60		68	64	60		67	63	60
9	77	67	61	57		75	67	61	57		66	61	57		65	60	57		64	60	57
10	73	64	58	54		72	63	58	54		62	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	716510
5°	734130
10°	742996
15°	707806
20°	624071
25°	504768
30°	341436
35°	171090
40°	27756
45°	27164
50°	27707
55°	28116
60°	28910
65°	29576
70°	30253
75°	30606
80°	29510
85°	24571

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 30606 cd/sqm



TEST NUMBER: P751158

CATALOG NUMBER: LD4D60D010-EU4DR6055659035-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	639.7	11.6
10°-20°	1730.8	31.3
20°-30°	1862.2	33.7
30°-40°	809.5	14.7
40°-50°	135.9	2.5
50°-60°	132.2	2.4
60°-70°	113.1	2.0
70°-80°	75.6	1.4
80°-90°	22.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4232.8	76.7
0°-40°	5042.3	91.3
0°-60°	5310.4	96.2
0°-90°	5521.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5521.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6558	
5°	6694	640
15°	6257	1731
25°	4187	1862
35°	1283	809
45°	176	136
55°	148	132
65°	114	113
75°	72	76
85°	20	23
90°	0	



TEST NUMBER: P751158

CATALOG NUMBER: LD4D60D010-EU4DR6055659035-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6557.8
2.5°	6742.2
5°	6693.5
7.5°	6708.9
10°	6696.9
12.5°	6558.7
15°	6257.4
17.5°	5852.9
20°	5367.3
22.5°	4847.5
25°	4187.0
27.5°	3348.9
30°	2706.3
32.5°	2085.8
35°	1282.7
37.5°	548.8
40°	194.6
42.5°	179.2
45°	175.8
47.5°	169.8
50°	163.0
52.5°	155.3
55°	147.6
57.5°	140.0
60°	132.3
62.5°	123.7
65°	114.4
67.5°	105.0
70°	94.7
72.5°	83.6
75°	72.5
77.5°	59.7
80°	46.9
82.5°	33.3
85°	19.6
87.5°	6.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)