

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751233

Luminaire Tested: LD4D60D010-EU4DR6555659035-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3968.6 lumens
Efficiency: N/A
Efficacy: 61.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751233

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P751233

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	89	84	79	95	88	83	79	86	82	78		84	80	77		82
5	92	83	78	73	90	83	77	73	81	76	72		79	75	72		77
6	87	78	72	68	86	77	72	68	76	71	67		74	70	67		73
7	83	73	67	63	81	73	67	63	71	66	62		70	66	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	58	55		63	58	55		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	426915
5°	427262
10°	442310
15°	443038
20°	407897
25°	347551
30°	266053
35°	187963
40°	110952
45°	45042
50°	16335
55°	9105
60°	5223
65°	2870
70°	3003
75°	2364
80°	2454
85°	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45042 cd/sqm



TEST NUMBER: P751233

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.2	9.5
10°-20°	1085.3	27.3
20°-30°	1302.1	32.8
30°-40°	875.1	22.0
40°-50°	262.0	6.6
50°-60°	46.2	1.2
60°-70°	13.1	0.3
70°-80°	6.4	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2763.7	69.6
0°-40°	3638.7	91.7
0°-60°	3946.9	99.5
0°-90°	3968.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3968.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3907	
5°	3896	376
15°	3917	1085
25°	2883	1302
35°	1409	875
45°	292	262
55°	48	46
65°	11	13
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P751233

CATALOG NUMBER: LD4D60D010-EU4DR6555659035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3907.3
2.5°	3923.9
5°	3895.6
7.5°	3954.5
10°	3986.7
12.5°	3978.9
15°	3916.7
17.5°	3764.6
20°	3508.1
22.5°	3206.0
25°	2882.9
27.5°	2518.1
30°	2108.8
32.5°	1737.9
35°	1409.2
37.5°	1084.4
40°	777.9
42.5°	508.1
45°	291.5
47.5°	154.4
50°	96.1
52.5°	66.6
55°	47.8
57.5°	34.4
60°	23.9
62.5°	15.5
65°	11.1
67.5°	10.0
70°	9.4
72.5°	7.2
75°	5.6
77.5°	5.0
80°	3.9
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)