

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750779

Luminaire Tested: LD4D60D010-EU4DR3555659040-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3555659040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6078.9 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750779

CATALOG NUMBER: LD4D60D010-EU4DR3555659040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P750779

CATALOG NUMBER: LD4D60D010-EU4DR3555659040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1827517
5°	1784573
10°	1608377
15°	1248360
20°	708055
25°	275458
30°	102773
35°	56328
40°	36813
45°	22405
50°	14261
55°	10077
60°	7364
65°	4007
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22405 cd/sqm



TEST NUMBER: P750779

CATALOG NUMBER: LD4D60D010-EU4DR3555659040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1496.5	24.6
10°-20°	2921.7	48.1
20°-30°	1191.6	19.6
30°-40°	285.2	4.7
40°-50°	118.8	2.0
50°-60°	49.2	0.8
60°-70°	15.4	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5609.8	92.3
0°-40°	5894.9	97.0
0°-60°	6062.9	99.7
0°-90°	6078.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6078.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16726	
5°	16271	###
15°	11036	2922
25°	2285	1192
35°	422	285
45°	145	119
55°	53	49
65°	16	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750779

CATALOG NUMBER: LD4D60D010-EU4DR3555659040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	16726.2
2.5°	16625.9
5°	16271.0
7.5°	15563.2
10°	14496.9
12.5°	12995.5
15°	11036.2
17.5°	8639.9
20°	6089.6
22.5°	3883.0
25°	2284.9
27.5°	1291.6
30°	814.6
32.5°	571.9
35°	422.3
37.5°	326.6
40°	258.1
42.5°	198.8
45°	145.0
47.5°	108.5
50°	83.9
52.5°	66.6
55°	52.9
57.5°	42.9
60°	33.7
62.5°	24.6
65°	15.5
67.5°	5.5
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)