

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750862

Luminaire Tested: LD4D60D010-EU4DR4055659040-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR4055659040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7343.3 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750862

CATALOG NUMBER: LD4D60D010-EU4DR4055659040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P750862

CATALOG NUMBER: LD4D60D010-EU4DR4055659040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1868053
5°	1858978
10°	1757134
15°	1493786
20°	1018120
25°	424803
30°	133569
35°	62076
40°	34331
45°	15745
50°	7632
55°	4191
60°	2185
65°	776
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15745 cd/sqm



TEST NUMBER: P750862

CATALOG NUMBER: LD4D60D010-EU4DR4055659040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1582.6	21.6
10°-20°	3545.5	48.3
20°-30°	1774.8	24.2
30°-40°	325.3	4.4
40°-50°	89.8	1.2
50°-60°	21.1	0.3
60°-70°	4.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6903.0	94.0
0°-40°	7228.3	98.4
0°-60°	7339.2	99.9
0°-90°	7343.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7343.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17097	
5°	16949	###
15°	13206	3546
25°	3524	1775
35°	465	325
45°	102	90
55°	22	21
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750862

CATALOG NUMBER: LD4D60D010-EU4DR4055659040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	17097.2
2.5°	17072.2
5°	16949.4
7.5°	16557.8
10°	15837.7
12.5°	14715.1
15°	13205.9
17.5°	11243.3
20°	8756.3
22.5°	5969.7
25°	3523.7
27.5°	1862.7
30°	1058.7
32.5°	684.2
35°	465.4
37.5°	332.6
40°	240.7
42.5°	164.8
45°	101.9
47.5°	64.9
50°	44.9
52.5°	32.0
55°	22.0
57.5°	14.0
60°	10.0
62.5°	6.0
65°	3.0
67.5°	2.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)