

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752852

Luminaire Tested: LD4D70BD010-EU4DR7070959027-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR7070959027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6643.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752852

CATALOG NUMBER: LD4D70BD010-EU4DR7070959027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752852

CATALOG NUMBER: LD4D70BD010-EU4DR7070959027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	572876
5°	571445
10°	570208
15°	570055
20°	564482
25°	530253
30°	472722
35°	376900
40°	250272
45°	149620
50°	77562
55°	40765
60°	14422
65°	233
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 149620 cd/sqm



TEST NUMBER: P752852

CATALOG NUMBER: LD4D70BD010-EU4DR7070959027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	495.5	7.5
10°-20°	1421.1	21.4
20°-30°	2004.7	30.2
30°-40°	1730.6	26.1
40°-50°	775.0	11.7
50°-60°	202.9	3.1
60°-70°	13.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3921.3	59.0
0°-40°	5651.9	85.1
0°-60°	6629.8	99.8
0°-90°	6643.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6643.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5243	
5°	5210	495
15°	5040	1421
25°	4398	2005
35°	2826	1731
45°	968	775
55°	214	203
65°	1	13
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752852

CATALOG NUMBER: LD4D70BD010-EU4DR7070959027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5243.2
2.5°	5237.6
5°	5210.2
7.5°	5187.6
10°	5139.5
12.5°	5096.1
15°	5039.6
17.5°	4974.5
20°	4854.8
22.5°	4657.7
25°	4398.4
27.5°	4097.7
30°	3746.9
32.5°	3317.9
35°	2825.7
37.5°	2282.7
40°	1754.7
42.5°	1333.2
45°	968.3
47.5°	667.5
50°	456.3
52.5°	314.9
55°	214.0
57.5°	129.2
60°	66.0
62.5°	20.7
65°	0.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)