

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752159

Luminaire Tested: LD4D70BD010-EU4DR2570959030-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752159
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR2570959030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5367.0 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752159

CATALOG NUMBER: LD4D70BD010-EU4DR2570959030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752159

CATALOG NUMBER: LD4D70BD010-EU4DR2570959030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85		
5	100	93	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82		
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79		
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2224101
5°	2071469
10°	1477638
15°	870273
20°	541494
25°	297170
30°	135903
35°	51472
40°	23306
45°	14015
50°	5813
55°	3753
60°	2622
65°	1758
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14015 cd/sqm



TEST NUMBER: P752159

CATALOG NUMBER: LD4D70BD010-EU4DR2570959030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1623.2	30.2
10°-20°	2198.5	41.0
20°-30°	1163.4	21.7
30°-40°	287.2	5.4
40°-50°	70.1	1.3
50°-60°	18.4	0.3
60°-70°	6.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4985.0	92.9
0°-40°	5272.2	98.2
0°-60°	5360.7	99.9
0°-90°	5367.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5367.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20356	
5°	18887	###
15°	7694	2198
25°	2465	1163
35°	386	287
45°	91	70
55°	20	18
65°	7	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752159

CATALOG NUMBER: LD4D70BD010-EU4DR2570959030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	20355.9
2.5°	20021.4
5°	18886.8
7.5°	16607.5
10°	13318.5
12.5°	10068.0
15°	7693.7
17.5°	5996.1
20°	4657.1
22.5°	3492.6
25°	2465.0
27.5°	1653.0
30°	1077.2
32.5°	655.4
35°	385.9
37.5°	236.1
40°	163.4
42.5°	124.9
45°	90.7
47.5°	54.8
50°	34.2
52.5°	24.8
55°	19.7
57.5°	15.4
60°	12.0
62.5°	9.4
65°	6.8
67.5°	2.6
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)