

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751247

Luminaire Tested: LD4D60D010-EU4DR6555659040-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P751247
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5576.7 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751247

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P751247

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	89	84	79		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	83	78	73		90	83	77	73		81	76	72		79	75	72		77	74	71
6	87	78	72	68		86	77	72	68		76	71	67		74	70	67		73	69	66
7	83	73	67	63		81	73	67	63		71	66	62		70	66	62		69	65	62
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58
9	75	65	59	55		74	65	59	55		64	58	55		63	58	55		62	58	54
10	71	61	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	599918
5°	600411
10°	621554
15°	622585
20°	573190
25°	488384
30°	373873
35°	264138
40°	155909
45°	63291
50°	22947
55°	12782
60°	7342
65°	4033
70°	4249
75°	3293
80°	3461
85°	2883

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 63291 cd/sqm



TEST NUMBER: P751247

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	528.7	9.5
10°-20°	1525.1	27.3
20°-30°	1829.8	32.8
30°-40°	1229.7	22.1
40°-50°	368.1	6.6
50°-60°	65.0	1.2
60°-70°	18.5	0.3
70°-80°	9.0	0.2
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3883.6	69.6
0°-40°	5113.3	91.7
0°-60°	5546.3	99.5
0°-90°	5576.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5576.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5491	
5°	5474	529
15°	5504	1525
25°	4051	1830
35°	1980	1230
45°	410	368
55°	67	65
65°	16	18
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P751247

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5490.7
2.5°	5514.1
5°	5474.3
7.5°	5557.0
10°	5602.3
12.5°	5591.3
15°	5504.0
17.5°	5290.2
20°	4929.7
22.5°	4505.2
25°	4051.1
27.5°	3538.5
30°	2963.4
32.5°	2442.2
35°	1980.3
37.5°	1523.8
40°	1093.1
42.5°	713.9
45°	409.6
47.5°	216.9
50°	135.0
52.5°	93.6
55°	67.1
57.5°	48.4
60°	33.6
62.5°	21.8
65°	15.6
67.5°	14.0
70°	13.3
72.5°	10.1
75°	7.8
77.5°	7.0
80°	5.5
82.5°	3.9
85°	2.3
87.5°	1.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)