

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P751253

Luminaire Tested: LD4D60D010-EU4DR6555659040-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P751253
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR6555659040-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5578.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P751253

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P751253

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		111	108	105	103		104	102	100		100	99	97		97	95	94
2	107	102	97	94		105	100	96	92		97	93	90		94	91	88		91	89	87
3	101	94	88	84		99	92	87	83		90	86	82		87	84	81		85	82	80
4	95	87	81	76		93	86	80	76		84	79	75		82	77	74		80	76	73
5	90	81	74	70		88	80	74	69		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	64	59		79	69	63	59		68	63	59		67	62	58		66	61	58
8	76	66	59	55		75	65	59	55		64	58	54		63	58	54		62	57	54
9	72	61	55	51		71	61	55	51		60	54	51		59	54	50		58	54	50
10	68	58	52	47		67	57	51	47		57	51	47		56	51	47		55	50	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295798
5°	295052
10°	294798
15°	285711
20°	260107
25°	226667
30°	188526
35°	149376
40°	107812
45°	68108
50°	35499
55°	18868
60°	9905
65°	5445
70°	2288
75°	2527
80°	1749
85°	1474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 68108 cd/sqm



TEST NUMBER: P751253

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	479.0	8.6
10°-20°	1311.6	23.5
20°-30°	1603.2	28.7
30°-40°	1300.8	23.3
40°-50°	648.2	11.6
50°-60°	180.8	3.2
60°-70°	41.1	0.7
70°-80°	10.7	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3393.7	60.8
0°-40°	4694.5	84.2
0°-60°	5523.5	99.0
0°-90°	5578.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5578.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5065	
5°	5033	479
15°	4725	1312
25°	3517	1603
35°	2095	1301
45°	825	648
55°	185	181
65°	39	41
75°	11	11
85°	2	3
90°	0	



TEST NUMBER: P751253

CATALOG NUMBER: LD4D60D010-EU4DR6555659040-4LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	5064.7
2.5°	5061.0
5°	5032.7
7.5°	5016.3
10°	4970.9
12.5°	4878.7
15°	4725.3
17.5°	4485.7
20°	4185.0
22.5°	3860.5
25°	3517.4
27.5°	3150.5
30°	2795.5
32.5°	2444.9
35°	2095.1
37.5°	1746.0
40°	1414.1
42.5°	1103.0
45°	824.6
47.5°	574.6
50°	390.7
52.5°	269.4
55°	185.3
57.5°	125.0
60°	84.8
62.5°	58.8
65°	39.4
67.5°	20.1
70°	13.4
72.5°	12.7
75°	11.2
77.5°	7.4
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)