

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752313

Luminaire Tested: LD4D70BD010-EU4DR3570959030-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR3570959030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6478.8 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752313

CATALOG NUMBER: LD4D70BD010-EU4DR3570959030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P752313

CATALOG NUMBER: LD4D70BD010-EU4DR3570959030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1947726
5°	1901950
10°	1714164
15°	1330471
20°	754623
25°	293578
30°	109522
35°	60036
40°	39237
45°	23888
50°	15196
55°	10744
60°	7867
65°	4266
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23888 cd/sqm



TEST NUMBER: P752313

CATALOG NUMBER: LD4D70BD010-EU4DR3570959030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1594.9	24.6
10°-20°	3113.9	48.1
20°-30°	1270.0	19.6
30°-40°	303.9	4.7
40°-50°	126.6	2.0
50°-60°	52.4	0.8
60°-70°	16.4	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5978.8	92.3
0°-40°	6282.7	97.0
0°-60°	6461.7	99.7
0°-90°	6478.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6478.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17826	
5°	17341	###
15°	11762	3114
25°	2435	1270
35°	450	304
45°	155	127
55°	56	52
65°	16	16
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752313

CATALOG NUMBER: LD4D70BD010-EU4DR3570959030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	17826.4
2.5°	17719.4
5°	17341.2
7.5°	16586.9
10°	15450.4
12.5°	13850.2
15°	11762.1
17.5°	9208.2
20°	6490.1
22.5°	4138.5
25°	2435.2
27.5°	1376.6
30°	868.1
32.5°	609.5
35°	450.1
37.5°	348.0
40°	275.1
42.5°	211.9
45°	154.6
47.5°	115.7
50°	89.4
52.5°	71.0
55°	56.4
57.5°	45.7
60°	36.0
62.5°	26.2
65°	16.5
67.5°	5.8
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)