

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750639

Luminaire Tested: LD4D60D010-EU4DR2555659050-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR2555659050-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5644.0 lumens
Efficiency: N/A
Efficacy: 87.6 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750639

CATALOG NUMBER: LD4D60D010-EU4DR2555659050-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P750639

CATALOG NUMBER: LD4D60D010-EU4DR2555659050-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101		109	105	102	100		102	100	98		99	97	96		97	95	94
3	107	102	98	95		105	101	97	94		98	95	93		96	93	91		94	92	90
4	103	97	93	90		102	96	93	90		94	91	89		93	90	88		91	89	87
5	100	93	89	86		98	93	89	86		91	87	85		89	86	84		88	85	83
6	97	90	85	82		95	89	85	82		88	84	81		87	83	81		85	83	80
7	93	87	82	79		92	86	82	79		85	81	78		84	80	78		83	80	78
8	91	84	79	76		90	83	79	76		82	78	76		81	78	75		80	77	75
9	88	81	76	73		87	80	76	73		80	76	73		79	75	73		78	75	73
10	85	78	74	71		85	78	74	71		77	73	71		76	73	71		76	73	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2338879
5°	2178372
10°	1553891
15°	915180
20°	569435
25°	312505
30°	142918
35°	54127
40°	24518
45°	14741
50°	6119
55°	3943
60°	2753
65°	1861
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14741 cd/sqm



TEST NUMBER: P750639

CATALOG NUMBER: LD4D60D010-EU4DR2555659050-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1706.9	30.2
10°-20°	2311.9	41.0
20°-30°	1223.4	21.7
30°-40°	302.0	5.4
40°-50°	73.7	1.3
50°-60°	19.4	0.3
60°-70°	6.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5242.3	92.9
0°-40°	5544.3	98.2
0°-60°	5637.4	99.9
0°-90°	5644.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5644.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	21406	
5°	19862	###
15°	8091	2312
25°	2592	1223
35°	406	302
45°	95	74
55°	21	19
65°	7	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750639

CATALOG NUMBER: LD4D60D010-EU4DR2555659050-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	21406.4
2.5°	21054.6
5°	19861.5
7.5°	17464.5
10°	14005.8
12.5°	10587.6
15°	8090.7
17.5°	6305.6
20°	4897.4
22.5°	3672.9
25°	2592.2
27.5°	1738.4
30°	1132.8
32.5°	689.2
35°	405.8
37.5°	248.3
40°	171.9
42.5°	131.4
45°	95.4
47.5°	57.6
50°	36.0
52.5°	26.1
55°	20.7
57.5°	16.2
60°	12.6
62.5°	9.9
65°	7.2
67.5°	2.7
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)