

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752468

Luminaire Tested: LD4D70BD010-EU4DR4570959030-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR4570959030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6124.0 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752468

CATALOG NUMBER: LD4D70BD010-EU4DR4570959030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P752468

CATALOG NUMBER: LD4D70BD010-EU4DR4570959030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		98	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	91
3	105	99	95	91		103	98	94	91		95	92	89		93	90	88		91	89	87
4	100	94	89	85		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	83	80		86	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	77	75		80	77	74
7	89	81	75	72		87	80	75	72		79	74	71		78	74	71		77	73	71
8	85	77	72	68		84	76	71	68		75	71	68		74	70	67		73	70	67
9	82	73	68	65		81	73	68	65		72	68	65		71	67	64		71	67	64
10	79	70	65	62		78	70	65	62		69	65	62		68	64	61		68	64	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1182660
5°	1148988
10°	1099267
15°	1006068
20°	798155
25°	498306
30°	274645
35°	123326
40°	48565
45°	22884
50°	10862
55°	5677
60°	2797
65°	672
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22884 cd/sqm



TEST NUMBER: P752468

CATALOG NUMBER: LD4D70BD010-EU4DR4570959030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	984.3	16.1
10°-20°	2422.5	39.6
20°-30°	1918.4	31.3
30°-40°	638.8	10.4
40°-50°	126.8	2.1
50°-60°	28.8	0.5
60°-70°	4.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5325.3	87.0
0°-40°	5964.1	97.4
0°-60°	6119.7	99.9
0°-90°	6124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6124.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10824	
5°	10476	984
15°	8894	2423
25°	4133	1918
35°	925	639
45°	148	127
55°	30	29
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752468

CATALOG NUMBER: LD4D70BD010-EU4DR4570959030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	10824.2
2.5°	10753.5
5°	10476.0
7.5°	10247.0
10°	9908.1
12.5°	9456.9
15°	8894.2
17.5°	8047.9
20°	6864.5
22.5°	5454.7
25°	4133.4
27.5°	3026.6
30°	2176.9
32.5°	1480.5
35°	924.6
37.5°	548.3
40°	340.5
42.5°	223.9
45°	148.1
47.5°	95.4
50°	63.9
52.5°	42.6
55°	29.8
57.5°	19.6
60°	12.8
62.5°	6.8
65°	2.6
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)