

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752704

Luminaire Tested: LD4D70BD010-EU4DR6070959030-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752704
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6070959030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7142.3 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752704

CATALOG NUMBER: LD4D70BD010-EU4DR6070959030-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752704

CATALOG NUMBER: LD4D70BD010-EU4DR6070959030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	96	90	86	100	94	89	86	91	88	84		89	86	83		87
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	78	73	69	77	72	68		75	71	68		74
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	77	67	61	57	75	67	61	57	66	61	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	58	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	926793
5°	949582
10°	961050
15°	915531
20°	807213
25°	652895
30°	441635
35°	221309
40°	35900
45°	35137
50°	35832
55°	36384
60°	37389
65°	38237
70°	39133
75°	39598
80°	38193
85°	31842

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 39598 cd/sqm



TEST NUMBER: P752704

CATALOG NUMBER: LD4D70BD010-EU4DR6070959030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	827.5	11.6
10°-20°	2238.8	31.3
20°-30°	2408.8	33.7
30°-40°	1047.0	14.7
40°-50°	175.9	2.5
50°-60°	171.0	2.4
60°-70°	146.3	2.0
70°-80°	97.9	1.4
80°-90°	29.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5475.0	76.7
0°-40°	6522.1	91.3
0°-60°	6868.9	96.2
0°-90°	7142.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7142.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8482	
5°	8658	827
15°	8094	2239
25°	5416	2409
35°	1659	1047
45°	227	176
55°	191	171
65°	148	146
75°	94	98
85°	25	29
90°	0	



TEST NUMBER: P752704

CATALOG NUMBER: LD4D70BD010-EU4DR6070959030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8482.4
2.5°	8720.8
5°	8657.9
7.5°	8677.8
10°	8662.3
12.5°	8483.5
15°	8093.8
17.5°	7570.6
20°	6942.4
22.5°	6270.2
25°	5415.7
27.5°	4331.7
30°	3500.5
32.5°	2697.9
35°	1659.2
37.5°	709.8
40°	251.7
42.5°	231.8
45°	227.4
47.5°	219.7
50°	210.8
52.5°	200.9
55°	191.0
57.5°	181.0
60°	171.1
62.5°	160.1
65°	147.9
67.5°	135.8
70°	122.5
72.5°	108.2
75°	93.8
77.5°	77.3
80°	60.7
82.5°	43.1
85°	25.4
87.5°	8.8
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)