

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P750797

Luminaire Tested: LD4D60D010-EU4DR3555659050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P750797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D60D010-EU4DR3555659050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6766.8 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 64.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P750797

CATALOG NUMBER: LD4D60D010-EU4DR3555659050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P750797

CATALOG NUMBER: LD4D60D010-EU4DR3555659050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108	112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101	108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94	105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89	101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85	98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81	94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78	91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74	88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72	86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69	83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2034315
5°	1986512
10°	1790373
15°	1389618
20°	788167
25°	306634
30°	114392
35°	62703
40°	40992
45°	24939
50°	15876
55°	11220
60°	8216
65°	4473
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24939 cd/sqm



TEST NUMBER: P750797

CATALOG NUMBER: LD4D60D010-EU4DR3555659050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1665.8	24.6
10°-20°	3252.3	48.1
20°-30°	1326.4	19.6
30°-40°	317.4	4.7
40°-50°	132.3	2.0
50°-60°	54.8	0.8
60°-70°	17.1	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6244.6	92.3
0°-40°	6562.0	97.0
0°-60°	6749.0	99.7
0°-90°	6766.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6766.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18619	
5°	18112	###
15°	12285	3252
25°	2544	1326
35°	470	317
45°	161	132
55°	59	55
65°	17	17
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P750797

CATALOG NUMBER: LD4D60D010-EU4DR3555659050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	18618.9
2.5°	18507.2
5°	18112.2
7.5°	17324.3
10°	16137.3
12.5°	14466.0
15°	12285.0
17.5°	9617.6
20°	6778.6
22.5°	4322.4
25°	2543.5
27.5°	1437.8
30°	906.7
32.5°	636.6
35°	470.1
37.5°	363.5
40°	287.4
42.5°	221.4
45°	161.4
47.5°	120.8
50°	93.4
52.5°	74.1
55°	58.9
57.5°	47.7
60°	37.6
62.5°	27.4
65°	17.3
67.5°	6.1
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)