

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752109

Luminaire Tested: LD4D65D010-EU4DR7055659040-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D65D010-EU4DR7055659040-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7479.1 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752109

CATALOG NUMBER: LD4D65D010-EU4DR7055659040-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P752109

CATALOG NUMBER: LD4D65D010-EU4DR7055659040-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	644977
5°	643372
10°	641968
15°	641792
20°	635524
25°	596993
30°	532221
35°	424344
40°	281765
45°	168456
50°	87335
55°	45908
60°	16236
65°	284
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 168456 cd/sqm



TEST NUMBER: P752109

CATALOG NUMBER: LD4D65D010-EU4DR7055659040-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	557.8	7.5
10°-20°	1599.9	21.4
20°-30°	2257.0	30.2
30°-40°	1948.4	26.1
40°-50°	872.6	11.7
50°-60°	228.4	3.1
60°-70°	14.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4414.8	59.0
0°-40°	6363.2	85.1
0°-60°	7464.2	99.8
0°-90°	7479.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7479.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5903	
5°	5866	558
15°	5674	1600
25°	4952	2257
35°	3181	1948
45°	1090	873
55°	241	228
65°	1	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752109

CATALOG NUMBER: LD4D65D010-EU4DR7055659040-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5903.1
2.5°	5896.7
5°	5866.0
7.5°	5840.5
10°	5786.3
12.5°	5737.5
15°	5673.8
17.5°	5600.6
20°	5465.8
22.5°	5243.9
25°	4952.0
27.5°	4613.4
30°	4218.5
32.5°	3735.5
35°	3181.4
37.5°	2569.9
40°	1975.5
42.5°	1501.0
45°	1090.2
47.5°	751.6
50°	513.8
52.5°	354.5
55°	241.0
57.5°	145.4
60°	74.3
62.5°	23.4
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)