

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752176

Luminaire Tested: LD4D70BD010-EU4DR2570959035-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR2570959035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6125.0 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752176

CATALOG NUMBER: LD4D70BD010-EU4DR2570959035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752176

CATALOG NUMBER: LD4D70BD010-EU4DR2570959035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2538193
5°	2364002
10°	1686306
15°	993173
20°	617967
25°	339136
30°	155093
35°	58742
40°	26600
45°	15993
50°	6646
55°	4286
60°	2994
65°	2017
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15993 cd/sqm

TEST NUMBER: P752176

CATALOG NUMBER: LD4D70BD010-EU4DR2570959035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1852.4	30.2
10°-20°	2508.9	41.0
20°-30°	1327.7	21.7
30°-40°	327.8	5.4
40°-50°	80.0	1.3
50°-60°	21.1	0.3
60°-70°	7.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5689.0	92.9
0°-40°	6016.8	98.2
0°-60°	6117.8	99.9
0°-90°	6125.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6125.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23231	
5°	21554	###
15°	8780	2509
25°	2813	1328
35°	440	328
45°	104	80
55°	22	21
65°	8	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752176

CATALOG NUMBER: LD4D70BD010-EU4DR2570959035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	23230.6
2.5°	22848.8
5°	21554.0
7.5°	18952.8
10°	15199.3
12.5°	11489.8
15°	8780.2
17.5°	6842.9
20°	5314.8
22.5°	3985.8
25°	2813.1
27.5°	1886.5
30°	1229.3
32.5°	748.0
35°	440.4
37.5°	269.5
40°	186.5
42.5°	142.6
45°	103.5
47.5°	62.5
50°	39.1
52.5°	28.3
55°	22.5
57.5°	17.6
60°	13.7
62.5°	10.7
65°	7.8
67.5°	2.9
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)