

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752289

Luminaire Tested: LD4D70BD010-EU4DR3570959024-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752289
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR3570959024-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5206.0 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752289

CATALOG NUMBER: LD4D70BD010-EU4DR3570959024-4LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P752289

CATALOG NUMBER: LD4D70BD010-EU4DR3570959024-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1565062
5°	1528288
10°	1377387
15°	1069073
20°	606363
25°	235904
30°	88012
35°	48245
40°	31535
45°	19191
50°	12222
55°	8629
60°	6315
65°	3438
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19191 cd/sqm

TEST NUMBER: P752289

CATALOG NUMBER: LD4D70BD010-EU4DR3570959024-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1281.5	24.6
10°-20°	2502.1	48.1
20°-30°	1020.5	19.6
30°-40°	244.2	4.7
40°-50°	101.8	2.0
50°-60°	42.1	0.8
60°-70°	13.2	0.3
70°-80°	0.3	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4804.1	92.3
0°-40°	5048.3	97.0
0°-60°	5192.3	99.7
0°-90°	5206.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5206.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14324	
5°	13934	###
15°	9451	2502
25°	1957	1020
35°	362	244
45°	124	102
55°	45	42
65°	13	13
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752289

CATALOG NUMBER: LD4D70BD010-EU4DR3570959024-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	14324.1
2.5°	14238.1
5°	13934.3
7.5°	13328.1
10°	12414.9
12.5°	11129.1
15°	9451.2
17.5°	7399.1
20°	5215.0
22.5°	3325.4
25°	1956.8
27.5°	1106.1
30°	697.6
32.5°	489.8
35°	361.7
37.5°	279.7
40°	221.1
42.5°	170.3
45°	124.2
47.5°	93.0
50°	71.9
52.5°	57.0
55°	45.3
57.5°	36.7
60°	28.9
62.5°	21.1
65°	13.3
67.5°	4.7
70°	0.8
72.5°	0.8
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)