

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752330

Luminaire Tested: LD4D70BD010-EU4DR3570959035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR3570959035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6891.6 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752330

CATALOG NUMBER: LD4D70BD010-EU4DR3570959035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P752330

CATALOG NUMBER: LD4D70BD010-EU4DR3570959035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2071824
5°	2023144
10°	1823391
15°	1415239
20°	802701
25°	312288
30°	116499
35°	63864
40°	41733
45°	25403
50°	16165
55°	11429
60°	8369
65°	4550
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25403 cd/sqm



TEST NUMBER: P752330

CATALOG NUMBER: LD4D70BD010-EU4DR3570959035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1696.5	24.6
10°-20°	3312.3	48.1
20°-30°	1350.9	19.6
30°-40°	323.3	4.7
40°-50°	134.7	2.0
50°-60°	55.8	0.8
60°-70°	17.5	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6359.7	92.3
0°-40°	6683.0	97.0
0°-60°	6873.5	99.7
0°-90°	6891.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6891.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18962	
5°	18446	###
15°	12512	3312
25°	2590	1351
35°	479	323
45°	164	135
55°	60	56
65°	18	17
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752330

CATALOG NUMBER: LD4D70BD010-EU4DR3570959035-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	18962.2
2.5°	18848.5
5°	18446.2
7.5°	17643.8
10°	16434.9
12.5°	14732.8
15°	12511.5
17.5°	9795.0
20°	6903.6
22.5°	4402.2
25°	2590.4
27.5°	1464.3
30°	923.4
32.5°	648.4
35°	478.8
37.5°	370.2
40°	292.6
42.5°	225.4
45°	164.4
47.5°	123.1
50°	95.1
52.5°	75.5
55°	60.0
57.5°	48.6
60°	38.3
62.5°	27.9
65°	17.6
67.5°	6.2
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)