

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752637

Luminaire Tested: LD4D70BD010-EU4DR5570959035-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5570959035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5526.5 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752637

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P752637

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	677100
5°	650205
10°	647760
15°	629146
20°	564121
25°	466214
30°	352173
35°	255348
40°	163411
45°	74632
50°	24409
55°	10534
60°	4523
65°	595
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 74632 cd/sqm



TEST NUMBER: P752637

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	564.1	10.2
10°-20°	1539.6	27.9
20°-30°	1754.5	31.7
30°-40°	1194.4	21.6
40°-50°	411.6	7.4
50°-60°	56.9	1.0
60°-70°	5.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3858.2	69.8
0°-40°	5052.5	91.4
0°-60°	5521.0	99.9
0°-90°	5526.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5526.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6197	
5°	5928	564
15°	5562	1540
25°	3867	1754
35°	1914	1194
45°	483	412
55°	55	57
65°	2	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752637

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6197.1
2.5°	6055.0
5°	5928.3
7.5°	5866.1
10°	5838.5
12.5°	5746.3
15°	5562.0
17.5°	5269.5
20°	4851.7
22.5°	4369.5
25°	3867.2
27.5°	3344.3
30°	2791.4
32.5°	2323.0
35°	1914.4
37.5°	1525.9
40°	1145.7
42.5°	794.0
45°	483.0
47.5°	260.3
50°	143.6
52.5°	85.2
55°	55.3
57.5°	35.3
60°	20.7
62.5°	9.2
65°	2.3
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)