

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752644

Luminaire Tested: LD4D70BD010-EU4DR5570959035-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752644
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5570959035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7010.1 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752644

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752644

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	858866
5°	824757
10°	821646
15°	798049
20°	715566
25°	591375
30°	446707
35°	323907
40°	207284
45°	94673
50°	30970
55°	13353
60°	5747
65°	750
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 94673 cd/sqm



TEST NUMBER: P752644

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	715.5	10.2
10°-20°	1952.9	27.9
20°-30°	2225.5	31.7
30°-40°	1515.0	21.6
40°-50°	522.1	7.4
50°-60°	72.2	1.0
60°-70°	7.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4893.9	69.8
0°-40°	6408.9	91.4
0°-60°	7003.2	99.9
0°-90°	7010.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7010.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7861	
5°	7520	716
15°	7055	1953
25°	4905	2225
35°	2428	1515
45°	613	522
55°	70	72
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752644

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7860.7
2.5°	7680.5
5°	7519.8
7.5°	7440.9
10°	7405.8
12.5°	7289.0
15°	7055.2
17.5°	6684.1
20°	6154.2
22.5°	5542.5
25°	4905.4
27.5°	4242.1
30°	3540.7
32.5°	2946.6
35°	2428.4
37.5°	1935.5
40°	1453.3
42.5°	1007.2
45°	612.7
47.5°	330.2
50°	182.2
52.5°	108.1
55°	70.1
57.5°	44.8
60°	26.3
62.5°	11.7
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)