

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752755

Luminaire Tested: LD4D70BD010-EU4DR6570959024-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P752755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6570959024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5093.0 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752755

CATALOG NUMBER: LD4D70BD010-EU4DR6570959024-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P752755

CATALOG NUMBER: LD4D70BD010-EU4DR6570959024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	89	84	79		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	83	78	73		90	83	77	73		81	76	72		79	75	72		77	74	71
6	87	78	72	68		86	77	72	68		76	71	67		74	70	67		73	69	66
7	83	73	67	63		81	73	67	63		71	66	62		70	66	62		69	65	62
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58
9	75	65	59	55		74	65	59	55		64	58	55		63	58	55		62	58	54
10	71	61	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	547877
5°	548325
10°	567634
15°	568573
20°	523460
25°	446021
30°	341449
35°	241223
40°	142387
45°	57805
50°	20958
55°	11677
60°	6687
65°	3697
70°	3865
75°	2997
80°	3146
85°	2633

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 57805 cd/sqm



TEST NUMBER: P752755

CATALOG NUMBER: LD4D70BD010-EU4DR6570959024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	482.8	9.5
10°-20°	1392.8	27.3
20°-30°	1671.1	32.8
30°-40°	1123.0	22.1
40°-50°	336.2	6.6
50°-60°	59.3	1.2
60°-70°	16.9	0.3
70°-80°	8.3	0.2
80°-90°	2.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3546.7	69.6
0°-40°	4669.7	91.7
0°-60°	5065.2	99.5
0°-90°	5093.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5093.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5014	
5°	4999	483
15°	5026	1393
25°	3700	1671
35°	1808	1123
45°	374	336
55°	61	59
65°	14	17
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P752755

CATALOG NUMBER: LD4D70BD010-EU4DR6570959024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5014.4
2.5°	5035.8
5°	4999.4
7.5°	5074.9
10°	5116.3
12.5°	5106.3
15°	5026.5
17.5°	4831.2
20°	4502.0
22.5°	4114.4
25°	3699.7
27.5°	3231.5
30°	2706.4
32.5°	2230.4
35°	1808.5
37.5°	1391.7
40°	998.3
42.5°	652.0
45°	374.1
47.5°	198.1
50°	123.3
52.5°	85.5
55°	61.3
57.5°	44.2
60°	30.6
62.5°	20.0
65°	14.3
67.5°	12.8
70°	12.1
72.5°	9.3
75°	7.1
77.5°	6.4
80°	5.0
82.5°	3.6
85°	2.1
87.5°	1.4
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)